




FREEslide

**Vorserienversion
Pre-series version**





<http://support.kesseboehmer.de/xxx>



4029070000

KESSEBÖHMER MA 12.0001.010.416.0000.00 06.03.2014



i				mm	
<p>KH: 320 - 360 LH: ≥ 280</p>	161	3,1 - 6,0 kg	O1us	xxxxxxxx	
		4,8 - 9,8 kg	O2us	xxxxxxxx	
		8,7 - 17,3 kg	O3us	xxxxxxxx	
				P1us	xxxxxxxx
<p>KH: 345 - 420 LH: ≥ 308</p> <p>!!!</p>	188	2,6 - 5,2 kg	P2us	xxxxxxxx	
		4,1 - 8,4 kg	P3us	xxxxxxxx	
		7,4 - 14,7 kg	P4us	xxxxxxxx	
		11,0 - 21,6 kg	Q1us	xxxxxxxx	
	<p>KH: 380 - 500 LH: ≥ 343</p>	223	2,2 - 4,3 kg	Q2us	xxxxxxxx
			3,4 - 7,1 kg	Q3us	xxxxxxxx
			6,3 - 12,4 kg	Q4us	xxxxxxxx
			9,3 - 18,3 kg	R1us	xxxxxxxx
	<p>KH: 430 - 600 LH: ≥ 388</p>	268	1,8 - 3,6 kg	R2us	xxxxxxxx
			2,8 - 5,9 kg	R3us	xxxxxxxx
			5,2 - 10,4 kg	R4us	xxxxxxxx
			7,7 - 15,2 kg		xxxxxxxx




4029070000

i				mm	
	450	16 19	324	xxxxxxxx	
	500	16 19	374	xxxxxxxx	
	600	16 19	474	xxxxxxxx	
	800	16 19	674	xxxxxxxx	
	900	16 19	774	xxxxxxxx	
	1000	16 19	874	xxxxxxxx	
	1200	16 19	1074	xxxxxxxx	
	1500	16 19	1374	xxxxxxxx	
	1800	16 19	1674	xxxxxxxx	
	KB	16 19	KB - (2 x K) - 88		

KESSEBÖHMER MA 12.0001.010.416.0000.00 06.03.2014

i

„mm“





KH	X	D	U	HH	T	V1	V2
320 - 360	157	274,5	KH - HH - K	278	≥ 281	128	177
345 - 420	185	302,5		328	≥ 333	146	205
380 - 500	220	337,5		390	≥ 393	168	240
430 - 600	265	382,5		470	≥ 473	196	284


4029070000

KESSEBÖHMER MA 12.0001.010.416.0000.00 06.03.2014


1




„mm“



2




3




4029070000

4




KH	X
320 - 360	157
345 - 420	185
380 - 500	220
430 - 600	265

KESSEBÖHMER MA 12.0001.010.416.0000.00 06.03.2014










6




5






7



i



4029070000

06.03.2014

KESSEBÖHMER MA 12.0001.010.416.0000.00